

Substation - Aluminum Rigid Spacer

By Burndy
 Catalog # [S3GBP48A13GS](#)



Three Conductor 13 IN Spacer, 1750 kcmil-2000 kcmil AAC, 1590(45/7) kcmil-1750(84/19) kcmil ACSR.

Application

Substation

General

Catalog Number	S3GBP48A13GS
Connector Type	Spacer
Material	Aluminum Alloy
Plating Type	Unplated
UPC	781810529362
UPC 12 Digit	7818105293622

Dimensions

Dimension - B Length inch	3.00 in
Dimension - Height inch	13.89 in
Dimension - Height mm	353 mm
Dimension - L Length Overall mm	399 mm
Dimension - Length Overall inch	15.69 in

Conductor Related

Conductor - ACSR Str Size Range	1590 (45/7) kcmil-1750 (84/19) kcmil
---------------------------------	--------------------------------------

Conductor - AL Str Size	1750 kcmil;1800 kcmil;1900 kcmil;2000 kcmil
Conductor - AL Str Size Range	1750 kcmil-2000 kcmil
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • ACSR C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - S3GBP48A13GS_MODEL-PDF](#)
- [3D Models - S3GBP48A13GS_MODEL-IGES](#)
- [3D Models - S3GBP48A13GS_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Specifications - S3GBP48A13GS](#)