

# SN10B, Nylon Splice For 12 - 10 AWG

By Burndy  
Catalog # SN10B



Nylon Splice For 12 - 10 AWG.

## Features

- Tin plated copper brazed butt seam
- Smooth funnel entry for easy wire insertion
- Nylon insulation offers high dielectric strength and stability

## Application

For Heavy Duty Application Requirements

## General

Catalog Number	SN10B
Color Code	Yellow
Connector Type	Braze Seam Butt Splice
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Nylon
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	INSULINK
Trade Name	INSULINK™
Type	SN
UPC	781810525081
UPC 12 Digit	781810525081

## Dimensions

Dimension - L Length Overall mm	42 mm
Dimension - Length Overall inch	1.64 in
Dimension - Outside Diameter inch	0.22 in
Dimension - Strip Length inch	3/8 in

## Electrical Ratings

Voltage - Maximum 600 V

## Conductor Related

Conductor - Copper Str Size Range	10 - 12 AWG
Conductor Size	12 - 10 AWG

## Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	100
Minimum Pack Quantity	50

## Product Assets

- [3D Models - SN10B\\_MODEL-STEP](#)
- [3D Models - SN10B\\_MODEL-PDF](#)
- [3D Models - SN10B\\_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_SN10\\_LineArt](#)
- [Sales Drawings - 50094193](#)
- [Specifications - SN10B](#)