

# T1010LF, Uninsulated Locking Fork Terminal For 12 - 10 AWG

By Burndy  
Catalog # T1010LF



Uninsulated Locking Fork Terminal For 12 - 10 AWG.

## Features

- Locking Fork Tongue design
- Allows for fast installation, screw only has to be loosened for termination
- Internal configuration of the fork prevents the terminal from coming off the screw without applying a pulling force
- Locking fork is made from copper alloy, permits many installation while maintaining proper spring retention of forks

## General

Catalog Number	T1010LF
Connector Type	Locking Fork Terminal
Feature - Barrel Style	Shrouded
Material	Copper
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Unplated
Trade Name	HYLUG™
UPC	781810530702
UPC 12 Digit	7818105307022

## Dimensions

Dimension - Bolt Size fraction	#8 - #10
Dimension - L Length Overall mm	23 mm
Dimension - Length Overall inch	0.90 in
Dimension - Pad Width inch	0.35 in
Dimension - Strip Length inch	11/32
Dimension - Stud Size inch	#8;#9;#10
Dimension - Z (inch)	0.29 in

## Conductor Related

Conductor Size	12 - 10 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	UI
Status	
UL Listed	No

## Logistics

Minimum Pack Quantity	100
-----------------------	-----

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50094175](#)  
[Specifications - T1010LF](#)