




## T1014, Uninsulated Ring Terminal For 12 - 10 AWG

By Burndy  
Catalog # T1014



Uninsulated Ring Terminal For 12 - 10 AWG.

## Features

Long neck terminal permits easy bending and stacking of several terminals on a common stud

## Application

For Control Wiring And Other Standard Duty Applications

## General

Catalog Number	T1014
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810722121
UPC 12 Digit	7818107221211

## Dimensions

Cable Insulation Diameter Maximum	0.12 in
Dimension - B Length fraction	17/50 in
Dimension - B Length inch	0.34 in
Dimension - Bolt Size fraction	1/4
Dimension - Diameter Max Size inch	0.12 in
Dimension - Hole Size fraction	10/37
Dimension - Hole Size inch	0.27 in
Dimension - L Length Overall mm	25 mm
Dimension - Length Overall inch	0.97 in
Dimension - Pad Width inch	0.46 in
Dimension - Strip Length inch	11/32
Dimension - Stud Size inch	1/4

Dimension - Z (inch) 0.39 in

## Conductor Related

Conductor - Copper Solid Size	12 AWG;11 AWG;10 AWG
Conductor - Copper Solid Size Range	12 AWG-10 AWG
Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Str-Size</li><li>• CU C Solid-Size</li></ul>

## Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	600
Minimum Pack Quantity	50
Pallet Quantity	99999

## Product Assets

[3D Models - T1014\\_MODEL-STEP](#)  
[3D Models - T1014\\_MODEL-IGES](#)  
[3D Models - T1014\\_MODEL-PDF](#)  
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_K6FT\\_LineArt](#)  
[Sales Drawings - 50094154](#)  
[Specifications - T1014](#)

