

# T108BF, Uninsulated Block Fork Terminal For 12 - 10 AWG

By Burndy  
Catalog # T108BF



Uninsulated Block Fork Terminal For 12 - 10 AWG.

## Features

- Permits rapid, easy installation of the terminal under the screw head without complete removal of the screw
- Designed to fit securely into terminal blocks

## General

Catalog Number	T108BF
Connector Type	Block Fork Terminal
Feature - Barrel Style	Shrouded
Material	Copper
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYDENT™
Type	Fork Tongue
UPC	781810530733
UPC 12 Digit	7818105307333

## Dimensions

Dimension - Bolt Size fraction	#6 - #8
Dimension - L Length Overall mm	23 mm
Dimension - Length Overall inch	0.90 in
Dimension - Pad Width inch	0.33 in

Dimension - Strip Length inch	11/32
Dimension - Stud Size inch	#6;#8
Dimension - Z (inch)	0.86 in

## Conductor Related

Conductor Size	12 - 10 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

## Logistics

Minimum Pack Quantity	100
-----------------------	-----

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50094180](#)  
[Specifications - T108BF](#)