

T1410BF, Uninsulated Block Fork Terminal For 16 - 14 AWG

By Burndy
Catalog # T1410BF



Uninsulated Block Fork Terminal For 16 - 14 AWG.

Features

- Permits rapid, easy installation of the terminal under the screw head without complete removal of the screw
- Designed to fit securely into terminal blocks

General

Catalog Number	T1410BF
Connector Type	Block Fork Terminal
Feature - Barrel Style	Shrouded
Material	Copper
Physical Attribute - Tongue Type	Block Fork
Plated	Y
Plating Type	Tin
Trade Name	HYDENT™
Type	Fork Tongue
UPC	781810530757
UPC 12 Digit	7818105307577

Dimensions

Dimension - Bolt Size fraction	#8 - #10
Dimension - L Length Overall mm	21
Dimension - Length Overall inch	0.83 in
Dimension - Pad Width inch	0.32 in
Dimension - Strip Length inch	9/32

Dimension - Stud Size inch	#8 - #10
Dimension - Z (inch)	0.79 in

Conductor Related

Conductor Range	#16 AWG to #14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50094180](#)
[Specifications - T1410BF](#)