



T1438, Uninsulated Ring Terminal For 16 - 14 AWG

By Burndy
Catalog # [T1438](#)

Uninsulated Ring Terminal For 16 - 14 AWG.



Features

Long neck terminal permits easy bending and stacking of several terminals on a common stud

Application

For Control Wiring And Other Standard Duty Applications

General

Catalog Number	T1438
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810722527
UPC 12 Digit	7818107225277

Dimensions

Dimension - B Length fraction	13/50 in
Dimension - B Length inch	0.26 in
Dimension - Bolt Size fraction	3/8
Dimension - Diameter Max Size inch	0.08 in
Dimension - Hole Size fraction	23/59
Dimension - Hole Size inch	0.39 in
Dimension - L Length Overall mm	26
Dimension - Length Overall inch	1.03 in
Dimension - Pad Width inch	0.53 in
Dimension - Strip Length inch	9/32
Dimension - Stud Size inch	3/8 in
Dimension - Z (inch)	0.51 in

Conductor Related

Conductor Range	#20 AWG to #14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1200
Minimum Pack Quantity	100
Pallet Quantity	99999

Product Assets

[3D Models - T1438_MODEL-STEP](#)

[3D Models - T1438_MODEL-PDF](#)

[3D Models - T1438_MODEL-IGES](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) - BUR_K6FT_LineArt](#)

[Sales Drawings - 50094154](#)

[Specifications - T1438](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-T1438-SPEC-EN | REV 8/2024