

# Uninsulated Ring Terminal For 16 - 14 AWG

By Burndy  
Catalog # T144



Uninsulated Ring Terminal For 16 - 14 AWG.

## General

Connector Type	Ring Terminal
Feature - Barrel Style	Chamfered
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810722329
UPC 12 Digit	7818107223299

## Dimensions

Dimension - Bolt Size fraction	#3 - #4
Dimension - Hole Size fraction	3/25
Dimension - Hole Size inch	0.12 in
Dimension - L Length Overall mm	17
Dimension - Length Overall inch	0.66 in
Dimension - Pad Width inch	0.25 in
Dimension - Strip Length inch	9/32
Dimension - Stud Size inch	#3 - #4
Dimension - Z inch	0.28 in

## Conductor Related

Conductor Range	#20 AWG to #14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	1200
Minimum Pack Quantity	100
Pallet Quantity	99999

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50094154](#)