

T146F, Uninsulated Fork Terminal For 16 - 14 AWG

By Burndy
Catalog # T146F



Uninsulated Fork Terminal For 16 - 14 AWG.

Application

For Control Wiring And Other Standard Duty Applications

General

Catalog Number	T146F
Connector Type	Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	T-F
UPC	781810722343
UPC 12 Digit	7818107223433

Dimensions

Dimension - B Length fraction	13/50 in
Dimension - B Length inch	0.26 in
Dimension - Bolt Size fraction	#4 - #6
Dimension - Diameter Max Size inch	0.07 in
Dimension - L Length Overall mm	17
Dimension - Length Overall inch	0.68 in
Dimension - Pad Width inch	0.28 in
Dimension - Strip Length inch	9/32 in
Dimension - Stud Size inch	#4 - #6
Dimension - Z (inch)	0.25 in

Conductor Related

Conductor Range	#20 AWG to #14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	1200
Minimum Pack Quantity	100
Pallet Quantity	99999

Product Assets

[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_tfla](#)
[Sales Drawings - 50094170](#)
[Specifications - T146F](#)