

# T168BF, Uninsulated Block Fork Terminal For 22 - 16 AWG

By Burndy  
Catalog # T168BF



## Features

- Permits rapid, easy installation of the terminal under the screw head without complete removal of the screw
- Designed to fit securely into terminal blocks

## General

Catalog Number	T168BF
Connector Type	Block Fork Terminal
Feature - Barrel Style	Shrouded
Material	Copper
Physical Attribute - Tongue Type	Block Fork
Plated	Y
Plating Type	Tin
Trade Name	HYDENT™
Type	Fork Tongue
UPC	781810530863
UPC 12 Digit	7818105308633

## Dimensions

Dimension - Bolt Size fraction	#6 - #8
Dimension - L Length Overall mm	21
Dimension - Length Overall inch	0.83 in
Dimension - Pad Width inch	0.31 in
Dimension - Strip Length inch	9/32 in

Dimension - Stud Size inch	#6 - #8
Dimension - Z (inch)	0.32 in

## Conductor Related

Conductor Range	#22 AWG to #18 AWG
Conductor Size	22 - 16 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

## Logistics

Minimum Pack Quantity	100
-----------------------	-----

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50094180](#)
- [Specifications - T168BF](#)