


T1814, Uninsulated Ring Terminal For 22 - 18 AWG

By Burndy
Catalog # T1814



Uninsulated Ring Terminal For 22 - 18 AWG.

Features

Long neck terminal permits easy bending and stacking of several terminals on a common stud

Application

For Control Wiring And Other Standard Duty Applications

General

Catalog Number	T1814
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810723166
UPC 12 Digit	7818107231666

Dimensions

Dimension - B Length fraction	13/50 in
Dimension - B Length inch	0.26 in
Dimension - Bolt Size fraction	1/4
Dimension - Diameter Max Size inch	0.06 in
Dimension - Hole Size fraction	1/4
Dimension - Hole Size inch	0.27 in
Dimension - L Length Overall mm	24
Dimension - Length Overall inch	0.95 in
Dimension - Pad Width inch	0.40 in
Dimension - Strip Length inch	9/32 in

Dimension - Stud Size inch	1/4 in
Dimension - Z (inch)	0.49 in

Conductor Related

Conductor Range	#22 AWG to #18 AWG
Conductor Size	22 - 18 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	1200
Minimum Pack Quantity	100
Pallet Quantity	99999

Product Assets

- [3D Models - T1814_MODEL-IGES](#)
- [3D Models - T1814_MODEL-PDF](#)
- [3D Models - T1814_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_K6FT_LineArt](#)
- [Sales Drawings - 50094154](#)
- [Specifications - T1814](#)