

## T1814F, Uninsulated Fork Terminal For 22 - 18 AWG

By Burndy  
Catalog # T1814F



Uninsulated Fork Terminal For 22 - 18 AWG.

### Features

- Fork terminals are constructed of pure electrolytic copper
- Long brazed seam barrel with deep V groove inner serrations for optimum conductivity, reliability and holding power after crimping
- Fork tongue design for faster installation - screw only needs to be loosened for termination
- Two or more terminals can be stacked on a common stud
- Provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating for durable, long lasting corrosion resistance
- Inspection hole/skive provides an easy visual check of proper wire insertion
- 600 Volts maximum, 105°C maximum

### Application

For Control Wiring And Other Standard Duty Applications

### General

Catalog Number	T1814F
Connector Type	Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	T-F
UPC	781810723142
UPC 12 Digit	7818107231422

### Dimensions

Dimension - Bolt Size fraction	1/4
Dimension - Hole Size fraction	2/7
Dimension - Hole Size inch	0.28 in

Dimension - L Length Overall mm	23
Dimension - Length Overall inch	0.92 in
Dimension - Pad Width inch	0.47 in
Dimension - Strip Length inch	9/32 in
Dimension - Stud Size inch	1/4 in
Dimension - Z (inch)	0.39 in

### Conductor Related

Conductor Range	#22 AWG to #18 AWG
Conductor Size	22 - 18 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

### Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	1200
Minimum Pack Quantity	100
Pallet Quantity	99999

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_tfla](#)  
[Sales Drawings - 50094170](#)  
[Specifications - T1814F](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-T1814F-SPEC-EN | REV 10/2024