

## Hardware

By Burndy  
Catalog # [TMHG42](#)

Stainless Steel Hardware Kit For I-Beam Connector, 1/2" Screw, 0.42" Max. Terminal Pad Thickness.



### Application

An irreversible compression ground connection which allows attachment to a structural steel standard (angled) or wide flange (para llel) beam.

### General

Connector Type	Hardware
EU RoHS Indicator	Yes
Material	STAINLESS STEEL
Sub Brand	INSULUG
Type	Compression Ground Connector
UPC	781810035054
UPC 12 Digit	7818100350544

### Dimensions

Dimension - Bolt Size fraction	1/2
Dimension - Thread Size	1/2 - 13

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"><li>UL 486A-B</li><li>IEEE 837</li></ul>
Standards - Industry Standards Met	<ul style="list-style-type: none"><li>UL 486A-B</li><li>IEEE 837</li></ul>
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	12
Minimum Pack Quantity	1
Pallet Quantity	5568

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_TMH\\_LineArt](#)  
[Sales Drawings - 50048710](#)