

## TMHG92, Stainless Steel Hardware Kit for I-Beam Connector (not included)



By Burndy  
Catalog # [TMHG92](#)

Stainless Steel Hardware Kit For I-Beam Connector, 1/2" Screw, 0.92" Max. Terminal Pad Thickness.

### Application

An irreversible compression ground connection which allows attachment to a structural steel standard (angled) or wide flange (parallel) beam.

### General

Catalog Number	TMHG92
Connector Type	Hardware
EU RoHS Indicator	Contact Manufacturer
Material	STAINLESS STEEL
Sub Brand	INSULUG
Type	Compression Ground Connector
UPC	781810035061
UPC 12 Digit	7818100350611

### Dimensions

Dimension - Bolt Size fraction	1/2
Dimension - Thread Size	1/2 - 13

### Certifications And Compliance

Buy American Compliant	Contact Manufacturer
------------------------	----------------------

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> <li>UL 486A-B</li> <li>IEEE 837</li> </ul>
Standards - Industry Standards Met	<ul style="list-style-type: none"> <li>UL 486A-B</li> <li>IEEE 837</li> </ul>
Standards - RoHS Compliance	CM
Status	
UL Listed	No

### Logistics

Carton Quantity	12
Minimum Pack Quantity	12
Pallet Quantity	5568

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_TMH\\_LineArt](#)  
[Sales Drawings - 50048710](#)  
[Specifications - TMHG92](#)