

TMHG92, Stainless Steel Hardware Kit for I-Beam Connector (not included)



By Burndy
Catalog # [TMHG92](#)

Stainless Steel Hardware Kit For I-Beam Connector, 1/2" Screw, 0.92" Max. Terminal Pad Thickness.

Features

- TMH Tongue Mounted Hardware Kits ensure the proper type and amount of hardware necessary for each installation
- Packaged in separate sealed bags, they are convenient to use and eliminate mismatched quantities

Application

An irreversible compression ground connection which allows attachment to a structural steel standard (angled) or wide flange (para llel) beam.

General

Catalog Number	TMHG92
Connector Type	Hardware
EU RoHS Indicator	Contact Manufacturer
Material	STAINLESS STEEL
Sub Brand	INSULUG
Type	Compression Ground Connector
UPC	781810035061
UPC 12 Digit	7818100350611

Dimensions

Dimension - Bolt Size fraction	1/2
Dimension - Thread Size	1/2 - 13

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL 486A-B • IEEE 837
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL 486A-B • IEEE 837
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	12
Minimum Pack Quantity	12
Pallet Quantity	5568

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_TMH_LineArt](#)
[Sales Drawings - 50048710](#)
[Specifications - TMHG92](#)