

TP1012, Vinyl Ring Terminal For 12 - 10 AWG

By Burndy
Catalog # [TP1012](#)



Ring Tongue Terminal, Polyvinylchloride, 600 VOLTS MAX. 105 Deg C MAX.

Features

- Expanded insulation support accepts standard and large wire diameters providing lower inventory requirements and greater flexibility
- Funnel entry for easy wire insertion
- Manufactured of pure electrolytic copper to provide maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove serrations in the inner barrel provides added holding strength and better conductivity

Application

For Commercial And Light Duty Industrial Control And Power Circuit Applications

General

Catalog Number	TP1012
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	HYDENT
Trade Name	VINYLUG™
Type	Ring Tongue
UPC	781810524299
UPC 12 Digit	7818105242999

Dimensions

Cable Insulation Diameter Maximum	0.26 in
Dimension - Bolt Size fraction	1/2
Dimension - L Length Overall mm	38 mm

Dimension - Length Overall inch	1.51 in
Dimension - Pad Width inch	0.69 in
Dimension - Strip Length inch	19/64 in
Dimension - Stud Size inch	1/2 in
Dimension - Z (inch)	0.61 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	50

Product Assets

[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_TP1010_LineArt](#)
[Sales Drawings - 50093722](#)
[Specifications - TP1012](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-TP1012-SPEC-EN | REV 10/2024