

## TP108FBG25, Vinyl Fork Terminal For 12 - 10 AWG

By Burndy  
Catalog # [TP108FBG25](#)



Cu Fork Tongue Terminal, Smooth Entry, 10-12 AWG, 600 V, #8 Spade, 0.98" L, 0.31" W, Vinyl Insul, Tin Plated, Yellow (Insul Color), 25 Pcs./Bag.

### Features

- Fork terminals are constructed of pure electrolytic copper
- Long brazed seam barrel with deep V groove inner serrations for optimum conductivity, reliability and holding power after crimping
- Fork tongue design for faster installation - screw only needs to be loosened for termination
- Two or more terminals can be stacked on a common stud
- Provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating for durable, long lasting corrosion resistance
- Inspection hole/skive provides an easy visual check of proper wire insertion
- 600 Volts maximum, 105°C maximum

### Application

The Type TP-F is a fork tongue variation of the TP design and makes installation easier

### General

Catalog Number	TP108FBG25
Connector Type	Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Sub Brand	HYDENT
Trade Name	HYDENT™
Type	TP-F
UPC	781810486399
UPC 12 Digit	7818104863999

### Dimensions

Dimension - B Length fraction	17/50 in
Dimension - B Length inch	0.34 in
Dimension - Bolt Size fraction	#6 - #8
Dimension - Hole Size fraction	8/47
Dimension - Hole Size inch	0.17 in
Dimension - Length Overall inch	0.98 in
Dimension - Pad Width inch	0.31 in
Dimension - Stud Size inch	#6;#8
Dimension - Z (inch)	0.26 in

### Conductor Related

Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

### Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards	UL486
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

### Logistics

Minimum Pack Quantity	5
-----------------------	---

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 10104489](#)  
[Specifications - TP108FBG25](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-TP108FBG25-SPEC-EN | REV 10/2024