

TP1410RBG25, Vinyl Ring Terminal For 16 - 14 AWG

By Burndy
Catalog # [TP1410RBG25](#)



Vinyl Ring Terminal For 16 - 14 AWG.

General

Catalog Number	TP1410RBG25
Connector Type	Ring Terminal
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Trade Name	HYDENT™
Type	Ring Tongue
UPC	781810486450
UPC 12 Digit	7818104864500

Dimensions

Dimension - Bolt Size fraction	#10
Dimension - Stud Size inch	#10

Conductor Related

Conductor - Copper Solid Size	16 AWG;15 AWG;14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor - Copper Str Size	16 AWG;14 AWG

Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	5
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 10104489](#)
- [Specifications - TP1410RBG25](#)