



TP146LF, Vinyl Locking Fork Terminal For 16 - 14 AWG

By Burndy
Catalog # [TP146LF](#)

Vinyl Locking Fork Terminal For 16 - 14 AWG.



Features

- Locking fork tongue design allows fast installation
- Screw only has to be loosened for termination
- Internal configuration of the fork prevents the terminal from coming off the screw without applying a pulling force
- Locking fork is made from a copper alloy and permits many installations while maintaining proper spring retention of forks

Application

For Fast Installation And Security

General

Catalog Number	TP146LF
Color Code	Blue
Connector Type	Locking Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Locking Fork
Plated	Y
Plating Type	Tin
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Type	TP-LF, Locking
UPC	781810713655
UPC 12 Digit	7818107136555

Dimensions

Cable Insulation Diameter Maximum	0.18 in
Dimension - B Length fraction	13/50 in
Dimension - B Length inch	0.26 in
Dimension - Bolt Size fraction	#6
Dimension - Hole Size fraction	7/50
Dimension - Hole Size inch	0.14 in
Dimension - L Length Overall	22 mm
mm	

Dimension - Length Overall inch	0.87 in
Dimension - Pad Width inch	0.28 in
Dimension - Strip Length inch	1/4 in
Dimension - Stud Size inch	#6
Dimension - Z (inch)	0.23 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor Range	#16 AWG to #14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	1200
Minimum Pack Quantity	100
Pallet Quantity	99999

Product Assets

[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_TP1010LF_LineArt](#)
[Sales Drawings - 50094176](#)
[Specifications - TP146LF](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BRDY-TP146LF-SPEC-EN | REV 1/2025