



TP146Z, Vinyl Flanged Fork Terminal For 16 - 14 AWG

By Burndy
Catalog # [TP146Z](#)

Vinyl Flanged Fork Terminal For 16 - 14 AWG.



Features

- Flange fork tongue design allows fast installation as screw only has to be loosened for termination
- The flanges on the end of the fork terminal aid in preventing a slightly loose terminal from becoming fully disconnected from the screw
- Flanges make re-securing a loose terminal easier

Application

For Fast Installation And Security

General

Catalog Number	TP146Z
Color Code	Blue
Connector Type	Flanged Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Flanged Fork
Plated	Y
Plating Type	Tin
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Type	Ring Tongue
UPC	781810712566
UPC 12 Digit	7818107125666

Dimensions

Cable Insulation Diameter Maximum	0.18 in
Dimension - Bolt Size fraction	#6
Dimension - Hole Size fraction	3/20
Dimension - Hole Size inch	0.15 in
Dimension - L Length Overall mm	21 mm
Dimension - Length Overall inch	0.83 in
Dimension - Pad Width inch	0.28 in

Dimension - Strip Length inch	1/4 in
Dimension - Stud Size inch	#6
Dimension - Z (inch)	0.23 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor Range	#16 AWG to #14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Certified Listed	Buy American Act Compliant (All status valid till December 2024)
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1200
Minimum Pack Quantity	100
Pallet Quantity	99999

Product Assets

[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_TP1410Z_LineArt](#)
[Sales Drawings - 50094185](#)
[Specifications - TP146Z](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BRDY-TP146Z-SPEC-EN | REV 1/2025