



## TP148RBG25, Vinyl Ring Terminal For 16 - 14 AWG

By Burndy  
Catalog # [TP148RBG25](#)



Vinyl Ring Terminal For 16 - 14 AWG.

### General

Catalog Number	TP148RBG25
Connector Type	Ring Terminal
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Trade Name	HYDENT™
Type	Ring Tongue
UPC	781810486511
UPC 12 Digit	7818104865111

### Dimensions

Dimension - Bolt Size fraction	#8
Dimension - Stud Size inch	#8

### Conductor Related

Conductor - Copper Solid Size Range	16 AWG;15 AWG;14 AWG
Conductor - Copper Solid Size	16 AWG-14 AWG
Conductor - Copper Str Size Range	16 AWG;14 AWG
Conductor - Copper Str Size	16 AWG - 14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

### Logistics

Minimum Pack Quantity	5
-----------------------	---

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 10104489](#)  
[Specifications - TP148RBG25](#)