

## TP1810FBG25, Vinyl Fork Terminal For 22 - 18 AWG

By Burndy  
Catalog # [TP1810FBG25](#)



Vinyl Fork Terminal For 22 - 18 AWG.

### General

Catalog Number	TP1810FBG25
Connector Type	Fork Terminal
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Trade Name	HYDENT™
UPC	781810486535
UPC 12 Digit	7818104865355

### Dimensions

Dimension - B Length fraction	13/50 in
Dimension - B Length inch	0.26 in
Dimension - Bolt Size fraction	#8 - #10
Dimension - Hole Size fraction	1/5
Dimension - Hole Size inch	0.20 in
Dimension - Length Overall inch	0.74 in
Dimension - Pad Width inch	0.36 in
Dimension - Stud Size inch	#8;#10

### Conductor Related

Conductor - Copper Str Size	20 AWG;18 AWG;16 AWG
Conductor - Copper Str Size Range	20 AWG - 16 AWG
Conductor Size	22 - 18 AWG
Conductor Type	CU C Str-Size

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	5
-----------------------	---

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 10104489](#)  
[Specifications - TP1810FBG25](#)