



TP1810RBG25, Vinyl Ring Terminal For 22 - 18 AWG

By Burndy
Catalog # TP1810RBG25



Vinyl Ring Terminal For 22 - 18 AWG.

General

Catalog Number	TP1810RBG25
Connector Type	Ring Terminal
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Trade Name	HYDENT™
Type	Ring Tongue
UPC	781810486559
UPC 12 Digit	7818104865599

Dimensions

Dimension - Bolt Size fraction	#10
Dimension - Stud Size inch	#10

Conductor Related

Conductor - Copper Solid Size	20 ;18 AWG
Conductor - Copper Solid Size Range	20 -18 AWG
Conductor - Copper Str Size	20 AWG;18 AWG
Conductor - Copper Str Size Range	20 AWG - 18 AWG
Conductor Size	22 - 18 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	5
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 10104489](#)
[Specifications - TP1810RBG25](#)



A Hubbell brand