

TP188RBG25, Vinyl Ring Terminal For 22 - 18 AWG

By Burndy
Catalog # TP188RBG25



Vinyl Ring Terminal For 22 - 18 AWG.

General

Catalog Number	TP188RBG25
Connector Type	Ring Terminal
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Trade Name	HYDENT™
Type	Ring Tongue
UPC	781810486610
UPC 12 Digit	7818104866100

Dimensions

Dimension - Bolt Size fraction	#8
Dimension - Stud Size inch	#8

Conductor Related

Conductor - Copper Solid Size	20 ;18 AWG
Conductor - Copper Solid Size Range	20 -18 AWG
Conductor - Copper Str Size	20 AWG;18 AWG

Conductor - Copper Str Size Range	20 AWG - 18 AWG
Conductor Size	22 - 18 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	5
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 10104489](#)
- [Specifications - TP188RBG25](#)