



Stainless Steel Circular Non-Butting Twin U Die, 600 kcmil, Green, Index 22

By Burndy
Catalog # U36RT

Non-Butting U Die, 600 kcmil, Green, Index 22.



Application

Crimping

General

Application - For Use On	Use with Y35, Y750, PAT750; Y46 and PAT46 with PUADP1 Adapter
Color Code	Green
Construction Material - Main	Stainless Steel
Crimp Force Capacity	12 ton
Die Index	22
Die Type	U Die
EU RoHS Indicator	Yes
Sub Brand	U-DIE
Type	Die
UPC	781810627426
UPC 12 Digit	7818106274266

Dimensions

Dimension - Width inch	0.75
Dimension - Width mm	19
Weight	0.2 lb

Conductor Related

Crimping Ranges 600 Kcmil

Certifications And Compliance

Standards - RoHS Compliance EX Status

Logistics

Carton Quantity 1
Minimum Pack Quantity 1
Package Contents Die only

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_u8crtla](#)
[Sales Drawings - 10102825](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-U36RT-SPEC-EN | REV 5/2024