



# Stainless Steel Circular Non-Butting Twin U Die, 750 kcmil, 600 Flex, Black, Index 24

By Burndy  
Catalog # U39RT

Non-Butting U Die, 750 kcmil, 600 Flex, Black, Index 24.



## Application

Crimping

## General

Application - For Use On	Use with Y35, Y750, PAT750; Y46 and PAT46 with PUADP1 Adapter
Color Code	Black
Construction Material - Main	Stainless Steel
Crimp Force Capacity	12 ton
Die Index	24
Die Type	U Die
EU RoHS Indicator	Yes
Sub Brand	U-DIE
Type	Die
UPC	781810627433
UPC 12 Digit	7818106274333

## Dimensions

Dimension - Width inch	1.38
Dimension - Width mm	35
Weight	0.26 lb

## Conductor Related

Crimping Ranges 750 Kcmil/600 Flex

## Certifications And Compliance

Standards - RoHS Compliance EX Status

## Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Package Contents	Die only

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_u8crtla](#)  
[Sales Drawings - 10102827](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-U39RT-SPEC-EN | REV 5/2024