



## UC25A12SLS, Parallel Tap, Aluminum Clamp

By Burndy  
Catalog # [UC25A12SLS](#)



Aluminum Clamp, Parallel Tap, 1/0 (Str.) AWG AL to 12 AWG CU.

### General

Catalog Number	UC25A12SLS
Installation Torque	180 in-lb
Recommended in-lb	
Material	Aluminum
Plated	N
Plating Type	Unplated
UPC	781810128442
UPC 12 Digit	7818101284422

### Dimensions

Dimension - Width inch	0.88 in
Dimension - Width mm	22 mm

### Conductor Related

Conductor - AL Str Size	1/0 AWG
Conductor - Copper Str Size	12 AWG

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

### Logistics

Carton Quantity	25
Minimum Pack Quantity	250
Pallet Quantity	7400

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_UC\\_PARA\\_CLAMP\\_LineArt](#)
- [Sales Drawings - 206755](#)
- [Specifications - UC25A12SLS](#)