

UC2W30, Copper Parallel Groove Clamp

By Burndy
Catalog # UC2W30



CU Parallel Groove Clamp accommodates large number of CU Conductors, Conductor: 2 Sol. - 300 (Either Groove).

Application

For Range Of Copper

General

Catalog Number	UC2W30
EU RoHS Indicator	Yes
Installation Torque	240 LBS/in
Recommended in-lb	
Plated	N
Plating Type	Unplated
Sub Brand	TAPIT
Type	UC
UPC	781810012871

Dimensions

Dimension - B Length fraction	2-7/8 in
Dimension - B Length inch	2.88 in
Dimension - Height fraction	2-3/16 in
Dimension - Height inch	2.18 in
Dimension - Width fraction	2 in

Conductor Related

Conductor - Copper Solid Size	2 AWG
Conductor - Copper Solid Size Range	2 AWG
Conductor - Copper Str Size	2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil
Conductor - Copper Str Size Range	2 AWG-300 kcmil

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - UC2W30_MODEL-STEP](#)
- [3D Models - UC2W30_MODEL-PDF](#)
- [3D Models - UC2W30_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_UC_PARA_CLAMP_LineArt](#)
- [Sales Drawings - SA..038990-01](#)
- [Specifications - UC2W30](#)