

UC32R, Parallel Groove Clamp Aluminum Alloy

By Burndy
Catalog # [UC32R](#)



High strength, high conductivity aluminum alloy. Properly proportioned to minimize stress corrosion and deterioration by galvanic action, length: 1-1/2", height: 2-3/8".

Features

- High strength, high conductivity, non-copper bearing aluminum alloy
- Properly proportioned to minimize stress corrosion and deterioration by galvanic action
- Keying tabs on connector body halves prevent mismatching
- Square shank, high strength galvanized steel bolt allows 1-wrench installation

Application

For All Combinations Of Copper, Aluminum, ACSR, 6201 And 5005

General

Catalog Number	UC32R
EU RoHS Indicator	Yes
Sub Brand	TAPIT
Type	UC-R
UPC	781810097106

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	25
-----------------------	----

Product Assets

[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - UC32R](#)