

UC32R, Parallel Groove Clamp Aluminum Alloy

By Burndy
Catalog # UC32R



High strength, high conductivity aluminum alloy. Properly proportioned to minimize stress corrosion and deterioration by galvanic action,length:1-1/2",height:2-3/8".

Features

- High strength, high conductivity, non-copper bearing aluminum alloy
- Properly proportioned to minimize stress corrosion and deterioration by galvanic action
- Keying tabs on connector body halves prevent mismatching
- Square shank, high strength galvanized steel bolt allows 1-wrench installation

Application

For All Combinations Of Copper, Aluminum, ACSR, 6201 And 5005

General

| | |
|-------------------|--------------|
| Catalog Number | UC32R |
| EU RoHS Indicator | Yes |
| Sub Brand | TAPIT |
| Type | UC-R |
| UPC | 781810097106 |

Certifications And Compliance

| | |
|------------------------------------|-----|
| Buy American Compliant | Yes |
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|----|
| Minimum Pack Quantity | 25 |
|-----------------------|----|

Product Assets

[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - UC32R](#)