



UC3444, Copper Parallel Groove Clamp, 500-1000 kcmil - Either Groove

By Burndy
Catalog # [UC3444](#)



CU Parallel Groove Clamp accommodates large number of CU Conductors, Conductor: 500 - 1000 (Either Groove).

General

Catalog Number	UC3444
Installation Torque	480 LBS/in
Recommended in-lb	
Plated	N
Plating Type	Unplated
UPC	781810012925

Dimensions

Dimension - B Length fraction	4-1/4 in
Dimension - B Length inch	4.25 in
Dimension - Height fraction	3-5/16 in
Dimension - Height inch	3.31 in
Dimension - Height mm	0 mm
Dimension - Width fraction	3-1/2 in
Dimension - Width inch	3.50 in

Conductor Related

Conductor - Copper Str Size	500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Size Range	500 kcmil-1000 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	4
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_UC_PARA_CLAMP_LineArt](#)
- [Sales Drawings - SA..038990-01](#)
- [Specifications - UC3444](#)