



UC8W26L, Cast Copper Alloy Universal Parallel Clamp, Tin Plated

By Burndy
Catalog # [UC8W26L](#)



Cast Copper Alloy Universal Parallel Clamp, 8 Sol. - 2/0 Str, 1 in Length, 1-7/16 in Width, Tin-plated

Application

For All Combinations Of Copper, Aluminum, ACSR, 6201, 5005, Steel And Copperweld

General

Catalog Number	UC8W26L
EU RoHS Indicator	Yes
Installation Torque	75 LBS/in
Recommended in-lb Plated	Yes
Plating Type	Tin - Electro Plated
Sub Brand	TAPIT
Type	UC-L, Universal
UPC	781810095959

Dimensions

Dimension - B Length inch	1 in
Dimension - Height fraction	1-1/2 in
Dimension - Height inch	1.45 in
Dimension - Width fraction	1-7/16 in
Dimension - Width inch	1.48 in

Conductor Related

Conductor - AAAC 5005 Size	30.58 (7) kcmil;48.69 (7) kcmil;77.47 (7) kcmil;123.3 (7) kcmil;155.4 (7) kcmil;195.7 (7) kcmil;246.9 (7) kcmil
Conductor - AAAC 5005 Size Range	30.58 (7) kcmil-246.9 (7) kcmil
Conductor - AAAC 6201 Size	30.58 (7) kcmil;48.69 (7) kcmil;77.47 (7) kcmil;123.3 (7) kcmil;155.4 (7) kcmil;195.7 (7) kcmil;246.9 (7) kcmil
Conductor - AAAC 6201 Size Range	30.58 (7) kcmil-246.9 (7) kcmil
Conductor - AL Str Size	8 AWG;6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - AL Str Size Range	8 AWG-2/0 AWG
Conductor - Copper Solid Size	8 -2/0
Conductor - Copper Solid Size Range	8 -2/0
Conductor - Copper Str Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Size A	8 - 2/0
Conductor - Copper Str Size A Range	8 - 2/0
Conductor - Copper Str Size B	8 - 2/0
Conductor - Copper Str Size B Range	8 - 2/0
Conductor - Copper Str Size Range	8 AWG-2/0 AWG
Conductor - CopperWeld C Solid Size	8 AWG;7 AWG
Conductor - CopperWeld Solid Size Range	8 AWG-7 AWG
Conductor - Galvanized Steel Str Size	5/32 (7) in;3/16 (7) in;7/32 (7) in;1/4 (7) in;9/32 (7) in;5/16 (7) in;3/8 (7) in;7/16 (7) in
Conductor - Galvanized Steel Str Size Range	5/32 (7) in-7/16 (7) in

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	RUS
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Carton Quantity	150
Minimum Pack Quantity	1
Pallet Quantity	7200

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_UCL_lineart](#)
- [Sales Drawings - SC..017162-01](#)
- [Specifications - UC8W26L](#)

