

UCG25R2R, Parallel Clamp, Aluminum

By Burndy

Catalog # [UCG25R2R](#)



Parallel Clamp, Cast Aluminum Alloy, 1.19" L, 1.71" Height, 1.46" W

General

Catalog Number	UCG25R2R
Installation Torque	240 LBS/in
Recommended in-lb	
Material	Aluminum
Plated	N
Plating Type	Unplated
Trade Name	TAPIT™
UPC	781810097755

Dimensions

Dimension - B Length fraction	1-1/5 in
Dimension - B Length inch	1.19 in
Dimension - Height fraction	1-5/7 in
Dimension - Height inch	1.71 in
Dimension - Width fraction	1-1/2 in
Dimension - Width inch	1.46 in

Conductor Related

Conductor - AAAC 5005 Size A	30.58 (7) kcmil;48.69 (7) kcmil;77.47 (7) kcmil;123.3 (7) kcmil
Conductor - AAAC 5005 Size A Range	30.58 (7) kcmil-123.3 (7) kcmil
Conductor - AAAC 5005 Size B	30.58 (7) kcmil;48.69 (7) kcmil;77.47 (7) kcmil
Conductor - AAAC 5005 Size B Range	30.58 (7) kcmil-77.47 (7) kcmil
Conductor - AAAC 6201 Size A	30.58 (7) kcmil;48.69 (7) kcmil;77.47 (7) kcmil;123.3 (7) kcmil
Conductor - AAAC 6201 Size A Range	30.58 (7) kcmil-123.3 (7) kcmil
Conductor - AAAC 6201 Size B	30.58 (7) kcmil;48.69 (7) kcmil;77.47 (7) kcmil
Conductor - AAAC 6201 Size B Range	30.58 (7) kcmil-123.3 (7) kcmil
Conductor - AL Str Size A	6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG
Conductor - AL Str Size A Range	6 AWG-1/0 AWG
Conductor - AL Str Size B	6 AWG;4 AWG;3 AWG;2 AWG

Conductor - AL Str Size B Range	6 AWG-2 AWG
Conductor - Copper Solid Size A	6 AWG
Conductor - Copper Solid Size A Range	6 AWG
Conductor - Copper Solid Size B	6 AWG
Conductor - Copper Solid Size B Range	6 AWG
Conductor - Copper Str Size A	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0
Conductor - Copper Str Size A Range	6 AWG-1/0
Conductor - Copper Str Size B	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size B Range	6 AWG-2 AWG
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size A • CU C Solid-Size A • CU C Str-Size A • AAAC C 5005-Size A • AAAC C 6201-Size A • AL C Str-Size B • CU C Solid-Size B • CU C Str-Size B • AAAC C 5005-Size B • AAAC C 6201-Size B

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

Catalogs - BURNDY Master Catalog - Section H - Overhead
Distribution
Customer Notices - Prop 65 Notice
Interactive Catalog - BURNDY Full-Line Digital Catalog

Product Cross Section Image(s) - BUR_UCGR_Lineart
Sales Drawings - sa042956-01
Specifications - UCG25R2R



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-UCG25R2R-SPEC-EN | REV 10/2024