

## UCG25R2RS, Parallel Clamp, Cast Aluminum Alloy

By Burndy  
Catalog # [UCG25R2RS](#)



Parallel Clamp, Cast Aluminum Alloy, 1.19" L, 1.71" Height, 1.46" W

### Features

- TAPIT Parallel Clamp
- High strength, high conductivity, non-copper bearing aluminum alloy
- Properly proportioned to minimize stress corrosion and deterioration by galvanic action
- Keying tabs on connector body halves prevent mismatching
- Square shank, high strength galvanized steel bolt allows one wrench installation

### General

Catalog Number	UCG25R2RS
Material	Aluminum
Plated	N
Plating Type	Unplated
Trade Name	TAPIT™
UPC	781810097786

### Dimensions

Dimension - B Length fraction	1-1/5 in
Dimension - B Length inch	1.19 in
Dimension - Height fraction	1-5/7 in
Dimension - Height inch	1.71 in
Dimension - Height mm	43.4 mm
Dimension - Width fraction	1-1/2 in
Dimension - Width inch	1.46 in

### Conductor Related

Conductor - AAAC 5005 Size A	30.58 (7) kcmil;48.69 (7) kcmil;77.47 (7) kcmil;123.3 (7) kcmil
Conductor - AAAC 5005 Size A Range	30.58 (7) kcmil-123.3 (7) kcmil
Conductor - AAAC 5005 Size B	30.58 (7) kcmil;48.69 (7) kcmil;77.47 (7) kcmil
Conductor - AAAC 5005 Size B Range	30.58 (7) kcmil-77.47 (7) kcmil
Conductor - AAAC 6201 Size A	30.58 (7) kcmil;48.69 (7) kcmil;77.47 (7) kcmil;123.3 (7) kcmil
Conductor - AAAC 6201 Size A Range	30.58 (7) kcmil-123.3 (7) kcmil

Conductor - AAAC 6201 Size B	30.58 (7) kcmil;48.69 (7) kcmil;77.47 (7) kcmil
Conductor - AAAC 6201 Size B Range	30.58 (7) kcmil-123.3 (7) kcmil
Conductor - AL Str Size A	6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG
Conductor - AL Str Size A Range	6 AWG-1/0 AWG
Conductor - AL Str Size B	6 AWG;4 AWG;3 AWG;2 AWG
Conductor - AL Str Size B Range	6 AWG-2 AWG
Conductor - Copper Solid Size A	6 AWG
Conductor - Copper Solid Size A Range	6 AWG
Conductor - Copper Solid Size B	6 AWG
Conductor - Copper Solid Size B Range	6 AWG
Conductor - Copper Str Size A	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0
Conductor - Copper Str Size A Range	6 AWG-1/0
Conductor - Copper Str Size B	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size B Range	6 AWG-2 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• AL C Str-Size A</li> <li>• CU C Solid-Size A</li> <li>• CU C Str-Size A</li> <li>• AAAC C 5005-Size A</li> <li>• AAAC C 6201-Size A</li> <li>• AL C Str-Size B</li> <li>• CU C Solid-Size B</li> <li>• CU C Str-Size B</li> <li>• AAAC C 5005-Size B</li> <li>• AAAC C 6201-Size B</li> </ul>

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	No	<a href="#">Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution</a>
<b>Logistics</b>		<a href="#">Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog</a>
Minimum Pack Quantity	1	<a href="#">Customer Notices - Prop 65 Notice</a>
<b>Product Assets</b>		<a href="#">Interactive Catalog - BURNDY Full-Line Digital Catalog</a>
		<a href="#">Product Cross Section Image(s) - BUR_UCGR_Lineart</a>
		<a href="#">Sales Drawings - sa042956-01</a>
		<a href="#">Specifications - UCG25R2RS</a>

