

UCG25R2RS, Parallel Clamp, Cast Aluminum Alloy

By Burndy
Catalog # [UCG25R2RS](#)



Parallel Clamp, Cast Aluminum Alloy, 1.19" L, 1.71" Height, 1.46" W

General

| | |
|----------------|--------------|
| Catalog Number | UCG25R2RS |
| Material | Aluminum |
| Plated | N |
| Plating Type | Unplated |
| Trade Name | TAPIT™ |
| UPC | 781810097786 |

Dimensions

| | |
|-------------------------------|----------|
| Dimension - B Length fraction | 1-1/5 in |
| Dimension - B Length inch | 1.19 in |
| Dimension - Height fraction | 1-5/7 in |
| Dimension - Height inch | 1.71 in |
| Dimension - Width fraction | 1-1/2 in |
| Dimension - Width inch | 1.46 in |

Conductor Related

| | |
|------------------------------------|---|
| Conductor - AAAC 5005 Size A | 30.58 (7) kcmil;48.69 (7) kcmil;77.47 (7) kcmil;123.3 (7) kcmil |
| Conductor - AAAC 5005 Size A Range | 30.58 (7) kcmil-123.3 (7) kcmil |
| Conductor - AAAC 5005 Size B | 30.58 (7) kcmil;48.69 (7) kcmil;77.47 (7) kcmil |
| Conductor - AAAC 5005 Size B Range | 30.58 (7) kcmil-77.47 (7) kcmil |
| Conductor - AAAC 6201 Size A | 30.58 (7) kcmil;48.69 (7) kcmil;77.47 (7) kcmil;123.3 (7) kcmil |
| Conductor - AAAC 6201 Size A Range | 30.58 (7) kcmil-123.3 (7) kcmil |
| Conductor - AAAC 6201 Size B | 30.58 (7) kcmil;48.69 (7) kcmil;77.47 (7) kcmil |
| Conductor - AAAC 6201 Size B Range | 30.58 (7) kcmil-123.3 (7) kcmil |
| Conductor - AL Str Size A | 6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG |
| Conductor - AL Str Size A Range | 6 AWG-1/0 AWG |
| Conductor - AL Str Size B | 6 AWG;4 AWG;3 AWG;2 AWG |
| Conductor - AL Str Size B Range | 6 AWG-2 AWG |

| | |
|---------------------------------------|--|
| Conductor - Copper Solid Size A | 6 AWG |
| Conductor - Copper Solid Size A Range | 6 AWG |
| Conductor - Copper Solid Size B | 6 AWG |
| Conductor - Copper Solid Size B Range | 6 AWG |
| Conductor - Copper Str Size A | 6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 |
| Conductor - Copper Str Size A Range | 6 AWG-1/0 |
| Conductor - Copper Str Size B | 6 AWG;5 AWG;4 AWG;3 AWG;2 AWG |
| Conductor - Copper Str Size B Range | 6 AWG-2 AWG |
| Conductor Type | <ul style="list-style-type: none"> AL C Str-Size A CU C Solid-Size A CU C Str-Size A AAAC C 5005-Size A AAAC C 6201-Size A AL C Str-Size B CU C Solid-Size B CU C Str-Size B AAAC C 5005-Size B AAAC C 6201-Size B |

Certifications And Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
[Customer Notices - Prop 65 Notice](#)



A Hubbell brand