



UCG25RS, Aluminum Alloy Parallel Clamp

By Burndy
Catalog # [UCG25RS](#)



Multiple purpose parallel groove clamp made of high strength, high conductivity aluminum alloy. Hardware allows for one of two wrench installation, length: 1-3/8", width: 1-5/8".

Application

For All Combinations Of Copper, Aluminum, ACSR, 6201 And 5005

General

Catalog Number	UCG25RS
EU RoHS Indicator	Yes
Material	Aluminum
Plated	N
Plating Type	Unplated
Sub Brand	TAPIT
Trade Name	TAPIT™
Type	UCG-RS
UPC	781810097809

Dimensions

Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.41 in
Dimension - Height fraction	2-1/8 in
Dimension - Height inch	2.09 in
Dimension - Width fraction	1-5/7 in
Dimension - Width inch	1.71 in
Dimension - Width mm	43 mm

Conductor Related

Conductor - AAAC 5005 Size A Range	30.58 (7) kcmil;48.69 (7) kcmil;77.47 (7) kcmil;123.3 (7) kcmil
Conductor - AAAC 5005 Size B Range	30.58 (7) kcmil-123.3 (7) kcmil
Conductor - AAAC 5005 Size A Range	30.58 (7) kcmil;48.69 (7) kcmil;77.47 (7) kcmil;123.3 (7) kcmil;155.4 (7) kcmil;195.7 (7) kcmil;246.9 (7) kcmil
Conductor - AAAC 5005 Size B Range	30.58 (7) kcmil-246.9 (7) kcmil
Conductor - AAAC 6201 Size A Range	30.58 (7) kcmil;48.69 (7) kcmil;77.47 (7) kcmil;123.3 (7) kcmil
Conductor - AAAC 6201 Size B Range	30.58 (7) kcmil-123.3 (7) kcmil
Conductor - AAAC 6201 Size A Range	30.58 (7) kcmil;48.69 (7) kcmil;77.47 (7) kcmil;123.3 (7) kcmil;155.4 (7) kcmil;195.7 (7) kcmil;246.9 (7) kcmil
Conductor - AAAC 6201 Size B Range	30.58 (7) kcmil-123.3 (7) kcmil
Conductor - AL Str Size A Range	8 AWG;6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG
Conductor - AL Str Size B Range	8 AWG-1/0 AWG
Conductor - AL Str Size A Range	8 AWG;6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG
Conductor - AL Str Size B Range	8 AWG-1/0 AWG
Conductor - Copper Str Size A Range	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0
Conductor - Copper Str Size B Range	8 AWG-1/0
Conductor - Copper Str Size A Range	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0
Conductor - Copper Str Size B Range	8 AWG-1/0
Conductor Type	<ul style="list-style-type: none">• AL C Str-Size A• CU C Solid-Size A• CU C Str-Size A• AAAC C 5005-Size A• AAAC C 6201-Size A• AL C Str-Size B• CU C Solid-Size B• CU C Str-Size B• AAAC C 5005-Size B• AAAC C 6201-Size B

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	1

Product Assets

[3D Models - UCG25RS_MODEL-STEP](#)
[3D Models - UCG25RS_MODEL-IGES](#)
[3D Models - UCG25RS_MODEL-PDF](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_UCGR_Lineart](#)
[Sales Drawings - sa042956-01](#)
[Specifications - UCG25RS](#)



A Hubbell brand