

UCG25RSCONKIT, Parallel Clamp Kit, includes UCG Clamp Connector and Cover

By Burndy

Catalog # [UCG25RSCONKIT](#)



CONTAINS UCG25RS AND COVER GROOVE A Al/Cu: 8Str-1/0Str ACSR: 6-1/0 GROOVE B Al/Cu: 8Str-1/0Str ACSR: 6-1/0
INCLUDES OXIDE INHIBITOR.

Application

Substation

General

Catalog Number	UCG25RSCONKIT
Connector Type	Split Bolt
Plated	N
Plating Type	Unplated
UPC	781810420331

Dimensions

Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.41 in
Dimension - Height inch	2.09 in
Dimension - Width fraction	1-5/7 in
Dimension - Width inch	1.71 in

Conductor Related

Conductor - Copper Str Size A Range	8 AWG-1/0 AWG
Conductor - Copper Str Size B Range	8 AWG-1/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	20
Minimum Pack Quantity	1
Pallet Quantity	1800

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 10056320](#)
[Specifications - UCG25RSCONKIT](#)