

# UCK3UL, Interlocking-finger Parallel Clamp, #6-2 AWG Sol/Str for Both Grooves; Tin-Plated Copper

By Burndy  
Catalog # [UCK3UL](#)



ACCOM: #6-2 AWG SOL/STR CU BOTH GROOVES TORQUE: 110 in-lbs; DURIMUM™ Silicon Bronze Hardware; Tin-plated, copper.

## General

Catalog Number	UCK3UL
Installation Torque	180 LBS/in
Recommended in-lb	
Material	Aluminum
Plated	N
Plating Type	Unplated
UPC	781810120866
UPC 12 Digit	7818101208666

## Dimensions

Dimension - Height fraction	1-7/16 in
Dimension - Height inch	1.4375 in
Dimension - Height mm	36.5 mm
Dimension - L Length Overall mm	25 mm
Dimension - Length Overall inch	1 in
Dimension - Width fraction	1-7/16 in
Dimension - Width inch	1.4375 in
Dimension - Width mm	37 mm

## Conductor Related

Conductor - Copper Solid Size A Range	6 Sol. - 2 Sol
Conductor - Copper Solid Size B Range	6 Str. - 2 Str
Conductor - Copper Str Size A Range	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG

Conductor - Copper Str Size A Range	6 Str. - 2 Str
Conductor - Copper Str Size B Range	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Size B Range	6 Str. - 2 Str

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	150
Minimum Pack Quantity	20
Pallet Quantity	14400

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_UCK\\_LineArt](#)
- [Sales Drawings - SD..210746-01](#)
- [Specifications - UCK3UL](#)