



# UCT26, FASTAP™ with LINEMAN ASSIST™ Aluminum Parallel Groove Clamp. Run: Cu/Al 8 Sol-2/0, ACSR 6-2/0; Tap: Cu/Al 6 Sol-2/0, ACSR: 6-2/0

By Burndy  
Catalog # UCT26



2/0 CU FASTAP PGC.

## General

Catalog Number	UCT26
Material	Copper
Plating	No
Plating Type	Unplated
Torque Rating	20 ft-lbs
Trade Name	FASTAP™
UPC	621945482647

## Dimensions

Dimensions	1.57 in x 2.67 in x 2.68 in
Height	2.68 in
Length	1.57 in
Width	2.67 in

## Conductor Related

Conductor - Copper Str Size A Range	8 Sol - 2/0 Str
Conductor - Copper Str Size B Range	8 Sol - 2/0 Str
Conductor Diameter (Main) - Maximum	0.45 in

Conductor Diameter (Main) - Minimum	0.13 in
Conductor Diameter (Main) Range	0.13 - 0.45
Conductor Diameter (Tap) - Maximum	0.45 in
Conductor Diameter (Tap) - Minimum	0.13 in

## Certifications And Compliance

Certification - CSA Approved	No
------------------------------	----

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50079618](#)
- [Sell Sheets - FASTAP™ with Lineman Assist™](#)
- [Specifications - UCT26](#)