



# UCT26, FASTAP™ with LINEMAN ASSIST™ Aluminum Parallel Groove Clamp.

By Burndy  
Catalog # UCT32



400 CU FASTAP PGC.

## Application

- Mechanical tapping of copper conductors in primary, secondary, and service drop applications
- Accommodates copper to copper applications

## General

Catalog Number	UCT32
Material	Copper
Plating	No
Plating Type	Unplated
Torque Rating	20 ft-lbs
Trade Name	FASTAP™
UPC	621945482654

## Dimensions

Dimensions	1.66 in x 2.84 in x 2.75 in
Height	2.75 in
Length	1.66 in
Width	2.84 in

## Conductor Related

Conductor - Copper Str Size A Range	1 Sol - 400 kcmil
Conductor - Copper Str Size B Range	8 Sol - 4/0 Str

Conductor Diameter (Main) - Maximum	0.73 in
Conductor Diameter (Main) - Minimum	0.29 in
Conductor Diameter (Main) Range	0.29 - 0.73
Conductor Diameter (Tap) - Maximum	0.56 in
Conductor Diameter (Tap) - Minimum	0.13 in

## Certifications And Compliance

Certification - CSA Approved	No
------------------------------	----

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50079618](#)
- [Specifications - UCT32](#)