

UCT32RSSS, Aluminum Parallel Groove Clamp featuring LINEMAN ASSIST

By Burndy
Catalog # UCT32RSSS



Aluminum Parallel Groove Clamp, Run: Cu & AL: 1 Sol. - 400, ACSR: 2 - 336.4, Tap: Cu & AL: 8 Sol. - 4/0, ACSR: 6 - 4/0, Stainless hardware.

Application

The system helps secure both the Tap and Run conductors while installing on primary, secondary and service lines. Connector is not recommended for Copper to Copper applications

General

Catalog Number	UCT32RSSS
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum
Plated	N
Plating Type	Unplated
Sub Brand	FASTAP
Trade Name	FASTAP™
Type	UCT
UPC	781810643884
UPC 12 Digit	7818106438844

Dimensions

Dimension - Height inch	2.62 in
Dimension - Height mm	0 mm
Dimension - Length Overall inch	1.62 in
Dimension - Width inch	2.82 in

Conductor Related

Conductor - AAAC 5005 Size Range	6 STR - 336.4
Conductor - AAAC 6201 Size Range	6 STR - 336.4
Conductor - ACSR Str Size Range	6 STR - 336.4
Conductor - ACSR Str Size A Range	2 Str. - 336.4
Conductor - ACSR Str Size B Range	6 Str. - 4/0

Conductor - AL Str Size A Range	1 SOL - 400
Conductor - AL Str Size B Range	1 Sol. - 400
Conductor - AL Str Size B Range	8 SOL - 4/0 STR
Conductor - Copper Solid Size Range	8 Sol. - 4/0 Str.
Conductor - Copper Solid Size Range	8-400
Conductor - Copper Solid Size Range	8-400
Conductor - Copper Str Size A Range	1 Sol. - 400
Conductor - Copper Str Size B Range	8 Sol. - 4/0 Str.
Conductor Type	<ul style="list-style-type: none"> • AAAC C 5005-Size • AAAC C 6201-Size • ACSR C Str-Size • AL C Str-Size A • AL C Str-Size B • CU C Solid-Size • CU C Str-Size A • CU C Str-Size B • CU Weld C Solid-Size

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	No
Standards - RoHS Compliance	UI
Status	

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50045569](#)
[Specifications - UCT32RSSS](#)