



Underground Connector Splice Kit

By Burndy
Catalog # [UGSKIT2](#)

Watertight Underground Splice Kit, 8-2 AWG, w/ Two Heavy Wall Heat Shrink Sleeves, Al/Cu Rated.



Application

For All Aluminum or Copper/Aluminum Combinations, UF Direct Burial

General

Connector Type	Splice/Heat Shrink Kit
EU RoHS Indicator	Yes
Hex Size	Slot
Material	Aluminum
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Sub Brand	SPLICE KIT
Temperature Rating	194
Type	UGSKIT, Watertight/Underground
UPC	781810175279

Dimensions

Dimension - L Length Overall mm	35 mm
Dimension - Length Overall inch	1.38 in

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Size	8 AWG;6 AWG;4 AWG;3 AWG;2 AWG
Conductor - AL Str Size Range	8 AWG-2 AWG
Conductor - Copper Str Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size Range	8 AWG-2 AWG
Conductor Size	8-2 AWG

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486D
Standards - Industry Standards Met	UL486D
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[3D Models - UGSKIT2_MODEL-IGES](#)
[3D Models - UGSKIT2_MODEL-STEP](#)
[3D Models - UGSKIT2_MODEL-PDF](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - SD..211382-01](#)



A proud member of the Hubbell Family.