



Underground Connector Splice Kit

By Burndy
Catalog # [UGSKIT8](#)

Direct Burial Splice Kit, 14-8 AWG, w/ Heavy Wall Heat Shrink Sleeve.



Features

- UGSKIT8 consists of a UF splice connector and a single heavy wall heat shrink sleeve
- The splice connector can accommodate up to four UF conductors and is installed with common installation tools
- Heavy wall heat shrink sleeve is lined with adhesive material to provide a watertight splice

Application

For UF Direct Burial

General

Connector Type	Splice/Heat Shrink Kit
EU RoHS Indicator	Yes
Hex Size	1/2
Material	Aluminum
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Sub Brand	SPLICE KIT
Temperature Rating	194
Type	UGSKIT8
UPC	781810175255

Dimensions

Dimension - L Length Overall mm	203 mm
Dimension - Length Overall inch	8.00 in

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Size	8 AWG
Conductor - AL Str Size Range	8 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG
Conductor - Copper Str Size Range	14 AWG-8 AWG
Conductor Size	14-8 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486D
Standards - Industry Standards Met	UL486D
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Product Cross Section Image\(s\) - BUR_UGSKIT8_LineArt](#)
[Sales Drawings - se212494-01](#)



A proud member of the Hubbell Family.