

UH165B, Substation Copper Bus Support

By Burndy
Catalog # UH165B



Copper Bus Connectors.

Features

- Type UH Copper Bus Supports for Supporting Copper Tube to Base
- High copper alloy bus support for mounting tube on a post or pedestal type insulator
- Single bolt allows rotation to any angle
- Rotate cap 180 degrees for slip or rigid fit
- Supplied with hardware for mounting to cap of insulator
- Suffix -B on the catalog number denotes base mounting hardware is supplied

Application

Substation

General

Catalog Number	UH165B
Connector Type	Bus Support
Fitting Type	Slip or Rigid
Hardware Type	Base mounting kit (w nuts)
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Mounting Hardware	5/8-11 x 1 3/4" LG
One Wrench Installation	Y
Plated	N
Plating Type	Unplated
Type	Cable or Tube to Insulator Bus Supports
UPC	781810327487
UPC 12 Digit	7818103274877

Dimensions

Bolt Circle Diameter	5 in
Dimension - G inch	2.38 in
Dimension - Height inch	3.56 in
Dimension - Height mm	90.4 mm
Dimension - Hole Size fraction	11/16

Dimension - Hole Size inch	0.69 in
Dimension - Width inch	3.50 in
Dimension - Width mm	89 mm

Conductor Related

Conductor - Connection Combination	Base to Tube
Conductor - Copper Tube EH Size	1 1/4 IPS IPS
Conductor - Copper Tube EH Size Range	1 1/4 IPS IPS
Conductor - Copper Tube Std Size	1 1/4 IPS IPS
Conductor - Copper Tube Std Size Range	1 1/4 IPS IPS
Conductor Type	<ul style="list-style-type: none"> • CU Tube Std-Size • CU Tube EH-Size
Number of Conductors	1

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - UH165B](#)