

UH225W, Substation Copper Bus Support, 4" IPS, 5" Bolt Dia, 5/8" Bolt

By Burndy
Catalog # UH225W



*Representative Image

Cast Cu Alloy Bus Support-Complete Part, 4" IPS, 5" Bolt Dia, 5/8" Bolt.

Application

Substation

General

Catalog Number	UH225W
Connector Type	Bus Support
Fitting Type	Slip or Rigid
Hardware Type	Cap mounting kit (w/o nuts)
Installation Torque	660 in-lb
Recommended in-lb	
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Mounting Hardware	5/8-11 x 1" LG
One Wrench Installation	Y
Plated	Y
Plating Type	Tin - Hot Dipped
Type	Cable or Tube to Insulator Bus Supports
UPC	781810119761
UPC 12 Digit	7818101197611

Dimensions

Bolt Circle Diameter	5 in
Dimension - B Length inch	3.25 in
Dimension - G inch	4.50 in
Dimension - Height inch	7.25 in
Dimension - Hole Size fraction	11/16
Dimension - Hole Size inch	0.69 in
Dimension - Width inch	7.50 in
Dimension - Width mm	191 mm

Conductor Related

Conductor - Connection Combination	Base to Tube
Conductor - Copper Tube EH Size	4 IPS
Conductor - Copper Tube EH Size Range	4 IPS
Conductor - Copper Tube Std Size	4 IPS
Conductor - Copper Tube Std Size Range	4 IPS
Conductor Type	<ul style="list-style-type: none"> • CU Tube Std-Size • CU Tube EH-Size
Number of Conductors	1

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - sa007374-01](#)
- [Specifications - UH225W](#)