

UHR153CG6, Substation Copper Bus Support

By Burndy
Catalog # [UHR153CG6](#)

Copper Bus Connectors.



Application

Substation

General

Catalog Number	UHR153CG6
Connector Type	Bus Support
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Type	Cable or Tube to Insulator Bus Supports
UPC	621945159358
UPC 12 Digit	6219451593588

Dimensions

Bolt Circle Diameter	3 in
Dimension - Height mm	0 mm
Dimension - Hole Size fraction	9/16
Dimension - Hole Size inch	0.56 in

Conductor Related

Conductor - Connection Combination	Base to Tube or Cable
Conductor - Copper Str Size	4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800

kcmil;850 kcmil;900 kcmil;1000 kcmil;1250 kcmil

Conductor - Copper Str Size Range
4/0 AWG-1250 kcmil

Conductor - Copper Tube Std Size
1/4 IPS ;3/8 IPS ;1/2 IPS ;3/4 IPS ;1 IPS

Conductor - Copper Tube Std Size Range
1/4 IPS -1 IPS

Number of Conductors 1

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity 6

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50061918](#)
- [Specifications - UHR153CG6](#)