

Stainless Steel Hexagonal Non-Butting Twin U Die, Index K1 1/2

By Burndy
Catalog # UK112T



Hexagonal Non-Butting U Die, Index K1 1/2.

Application

Crimping

General

Application - For Use On	Use with Y35, Y750, PAT750; Y46 and PAT46 with PUADP1 Adapter
Catalog Number	UK112T
Crimp Force Capacity	12 ton
Die Index	K1 1/2
Die Type	U Die
EU RoHS Indicator	Yes
Sub Brand	DIE SET
Type	Dies
UPC	781810006887
UPC 12 Digit	7818100068877

Certifications And Compliance

Standards - RoHS Compliance EX
Status

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Package Contents	Die only

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_UD3_LineArt](#)
[Sales Drawings - 30007595](#)
[Specifications - UK112T](#)