




## Stainless Steel UM Die Nest, #2 AWG DLO/Flex Cable

By Burndy  
Catalog # [UM2CN](#)



UM Die Nest, #2 AWG DLO/Flex Cable.

### Application

Crimping

### General

Application - For Use On	Use with OEM840NCP Pneumatic Press
Catalog Number	UM2CN
Crimp Force Capacity	12 ton
Die Type	UM Die
Tool Type	OEM Pneumatic
Type	Die
UPC	781810656976
UPC 12 Digit	7818106569766

### Certifications And Compliance

Standards - RoHS Compliance EX  
Status

### Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Package Contents	Die only

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50024694](#)  
[Specifications - UM2CN](#)