




Stainless Steel UM Die Indenter, #8 AWG DLO/Flex Cable

By Burndy
Catalog # [UMA](#)



UM Die Indenter, #8 AWG DLO/Flex Cable.

Application

Crimping

General

Application - For Use On	Use with OEM840NCP Pneumatic Press
Catalog Number	UMA
Crimp Force Capacity	12 ton
Die Type	UM Die
Tool Type	OEM Pneumatic
Type	Die
UPC	781810656921
UPC 12 Digit	7818106569211

Certifications And Compliance

Standards - RoHS Compliance EX
Status

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Package Contents	Die only

Product Assets

[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50024694](#)
[Specifications - UMA](#)