

# Stainless Steel UM Die Indenter, Press Dies, #6, #4, #2 AWG DLO/Flex Cable

By Burndy  
Catalog # [UMB](#)



UM Die Indenter, Press Dies, #6, #4, #2 AWG DLO/Flex Cable.

## Features

- Durable Stainless Steel Material
- Circumferential Crimp
- Indenter UM Die
- #6, #4, #2 AWG DLO/Flex Cable

## Application

Crimping

## General

Application - For Use On	Use with OEM840NCP Pneumatic Press
Catalog Number	UMB
Crimp Force Capacity	12 ton
Die Type	UM Die
Tool Type	OEM Pneumatic
Type	Die
UPC	781810657447

UPC 12 Digit 7818106574477

## Certifications And Compliance

Standards - RoHS Compliance EX  
Status

## Logistics

Carton Quantity 1  
Minimum Pack Quantity 1  
Package Contents Die only

## Product Assets

[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50024694](#)  
[Specifications - UMB](#)